

Small Platform Base



Small Platform Base, #53-009

Stock **#53-009** **9 In Stock**

1 **C\$471⁰⁰**

ADD TO CART

Volume Pricing

Qty 1+	C\$471.80 each
Need More?	Request Quote

Product Downloads

General

Imaging System Base **Type:**

Physical & Mechanical Properties

279.40 **Length (mm):**

11.0 **Length (inches):**

330.20 **Width (mm):**

13.0	Width (inches):
12.70	Thickness (mm):
0.5	Thickness (inches):
Anodized Aluminum	Construction:
8.00	Weight (lbs):

Threading & Mounting

(1) 3/4"-16 Tapped, (17) 1/4"-20 Tapped	Mounting Threads:
---	--------------------------

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:

Product Details

- Variety of Bases Available
- Stand-Alone or Benchtop Compatible Bases
- Designed for Use with 0.75" [Stainless Steel Posts](#)
- [Rack and Pinion Focusing Mounts](#), and [Accessories](#) also Available

Imaging System Bases are designed to construct imaging systems utilizing our 0.75" (19.05mm) diameter, 16 TPI mounting posts. The Large Workstation Platform and Small Platform Base feature sorbothane feet to minimize vibration. The Circular Base is weighted for added stability. The Universal Breadboard Adapter for 3/4" Posts features slots that allow for mounting to both metric and English [optical tables and breadboards](#). Imaging System Bases are available for a variety of system mounting and construction needs.

Technical Information

