

TECHSPEC[®] T-Mount Aperture Cap



#66-037: T-Mount Aperture Cap

Stock **#66-037** 20+ In Stock

-

1

+

C\$44⁴⁵

ADD TO CART

Volume Pricing	
Qty 1-4	C\$44.45 each
Qty 5-9	C\$39.76 each
Qty 10-25	C\$37.38 each
Need More?	Request Quote

Product Downloads

General

Tube Cap

Function:

Physical & Mechanical Properties

5.0

Total Length (mm):

4.00

Thickness (mm):

54.5	Extension Length (mm):
Threading & Mounting	
T-Mount	Thread Type:
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:

Product Details

- C, S, and T-Mount Solutions for Mounting Cube and Plate Beamsplitters, Filters, and Mirrors
 - Provides a 90° Mounting Interface
 - ¼-20 and M6 Tapped Mounting Threads for English or Metric Based Systems
- TECHSPEC® C, S, and T-Mount Cube and Plate Mounts allow for the integration of cube and plate optics into C, S, and T-Mount systems. These mounts feature four C, S, or T-Mount threaded apertures that can also act as connection points for other C, S, or T-Mount components. Either an M6 or 1/4-20 tapped hole is provided on the base for post mounting, making these mounts compatible with breadboard and benchtop systems. TECHSPEC C, S, and T-Mount Cube and Plate Mounts provide a 90° mounting interface ideal for placing beamsplitters, filters, and mirrors within a system. C, S, and T-Mount Aperture Caps are available to block light from unused openings and to protect the optic from dust and debris.

Note: #11-139 and #11-142 each include one S-Mount Aperture Cap (#11-137)

Technical Information

