

[See all 13 Products in Family](#)

TECHSPEC[®]

T-Mount, 60mm x 85mm Plate Mount, M6



Stock **#65-983** 3 In Stock

-

1

+

C\$742^{.00}

ADD TO CART

Volume Pricing	
Qty 1-4	C\$742.00 each
Qty 5-9	C\$655.90 each
Qty 10-25	C\$604.24 each
Need More?	Request Quote

Product Downloads

General	
Optic Mount (Fixed)	Function:
Rectangular	Type of Optics:
Note: Includes four T-Mount Aperture Caps (#66-037)	
Dimensions of Compatible Optics (mm): 60.0 x 85.0	

Physical & Mechanical Properties	
75.0 x 75.0 x 75.0	Dimensions (mm):
75.0	Extension Length (mm):
1.0	Min. Thickness of Compatible Optics (mm):
4.73	Max. Thickness of Compatible Optics (mm):
Threading & Mounting	
T-Mount	Thread Type:
M6 x 1.0	Compatible Post:
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 233:

Product Details

- C, S, and T-Mount Solutions for Mounting Cube and Plate Beamsplitters, Filters, and Mirrors
 - Provides a 90° Mounting Interface
 - 1/4-20 and M6 Tapped Mounting Threads for English or Metric Based Systems
- TECHSPEC® C, S, and T-Mount Cube and Plate Mounts allow for the integration of cube and plate optics into C, S, and T-Mount systems. These mounts feature four C, S, or T-Mount threaded apertures that can also act as connection points for other C, S, or T-Mount components. Either an M6 or 1/4-20 tapped hole is provided on the base for post mounting, making these mounts compatible with breadboard and benchtop systems. TECHSPEC C, S, and T-Mount Cube and Plate Mounts provide a 90° mounting interface ideal for placing beamsplitters, filters, and mirrors within a system. C, S, and T-Mount Aperture Caps are available to block light from unused openings and to protect the optic from dust and debris.
- Note:** [#11-139](#) and [#11-142](#) each include one S-Mount Aperture Cap ([#11-137](#))

Technical Information

