

[See all 13 Products in Family](#)

TECHSPEC® T-Mount, 40mm Cube Mount, M6



12.5mm x 17.5mm Plate S-Mount Holder



Stock **#63-982** **20+ In Stock**

⊖ 1 ⊕ C\$677⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-4	C\$677.60 each
Qty 5-9	C\$598.22 each
Qty 10-25	C\$550.76 each
Need More?	Request Quote

Product Downloads

General

Function:
Optic Mount (Fixed)

Type of Optics:
Cube

Note:
Includes four T-Mount Aperture Caps ([#66-037](#))

Dimensions of Compatible Optics (mm):

40.0 Sq.

Physical & Mechanical Properties

Dimensions (mm):

54.5 x 54.5 x 63.8

Extension Length (mm):

54.5

Min. Thickness of Compatible Optics (mm):

40.0

Max. Thickness of Compatible Optics (mm):

40.0

Threading & Mounting

Thread Type:

T-Mount

Compatible Post:

M6 x 1.0

Regulatory Compliance

RoHS 2015:

[Compliant](#)

Certificate of Conformance:

[View](#)

Reach 235:

[Compliant](#)

Product Details

- C, S, and T-Mount Solutions for Mounting Cube and Plate Beamsplitters, Filters, and Mirrors
- Provides a 90° Mounting Interface
- 1/4-20 and M6 Tapped Mounting Threads for English or Metric Based Systems

TECHSPEC® C, S, and T-Mount Cube and Plate Mounts allow for the integration of cube and plate optics into C, S, and T-Mount systems. These mounts feature four C, S, or T-Mount threaded apertures that can also act as connection points for other C, S, or T-Mount components. Either an M6 or 1/4-20 tapped hole is provided on the base for post mounting, making these mounts compatible with breadboard and benchtop systems. TECHSPEC C, S, and T-Mount Cube and Plate Mounts provide a 90° mounting interface ideal for placing beamsplitters, filters, and mirrors within a system. C, S, and T-Mount Aperture Caps are available to block light from unused openings and to protect the optic from dust and debris.

Note: #11-139 and #11-142 each include one S-Mount Aperture Cap (#11-137)

Technical Information

