

TECHSPEC[®] 23mm Diameter, T-Mount Eyepiece Mount



Stock #52-302 4 In Stock

-

1

+

C\$61^{.60}

ADD TO CART

Volume Pricing	
Qty 1+	C\$61.60 each
Need More?	Request Quote

Product Downloads

General	
Eyepiece Mount	Type:
Eyepiece	Type of Optics:
Optic Mount (Fixed)	Function:
1.25	Inner Diameter (inches):
Physical & Mechanical Properties	
	Length (mm):

28.45	
25.0	Extension Length (mm):
23.3	Inner Diameter (mm):
48.0	Outer Diameter (mm):
Threading & Mounting	
T-Mount	Thread Type:
Regulatory Compliance	
View	Certificate of Conformance:

Product Details

- Integrate Eyepieces into C and T-Mount Systems
- Feature Male C and T-Mount Thread
- Black Anodized Aluminum Construction

TECHSPEC® C and T-Mount Eyepiece Mounts are used to integrate microscope or telescope eyepieces into C and T-Mount systems. Eyepieces are placed within the inner diameter of the mounts where they are secured in place via a locking screw. Mounts #03-628 and #52-302 are designed to mount any DIN standard (23mm Dia.) microscope eyepieces, while mount #52-303 is designed to mount any American Standard (1.25in/31.7mm Dia.) telescope eyepieces. A black anodized finish increases the durability of these mounts, while also reducing stray light and reflections within the system. TECHSPEC C and T-Mount Eyepiece Mounts are ideal for integrating useful and versatile microscope and telescope eyepieces into digital camera systems. Mounts #52-302 and #52-303 feature both male and female T-Mount threads; mount #03-628 features only male C-Mount thread.