

TECHSPEC[®] 48mm, T-Mount Ring Mount, 1/4-20 Tapped Hole



Stock **#52-304** 20+ In Stock

-

1

+

C\$154^{.00}

ADD TO CART

Volume Pricing	
Qty 1-4	C\$154.00 each
Qty 5-9	C\$136.36 each
Qty 10-25	C\$126.28 each
Need More?	Request Quote

Product Downloads

General

Post Mounting Adapter

Function:

Physical & Mechanical Properties

20.00

Thickness (mm):

Black Anodized Aluminum (6061 T6)

Construction:

68.0	Outer Diameter (mm):
48.0	Inner Diameter (mm):

Threading & Mounting	
31.83	Mounting Flat to Center (mm):
T-Mount	Thread Type:
1/4-20	Compatible Post:

Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 235:

Product Details

- Allow for Post Mounting C, S, and T-Mount Tube System Assemblies
 - 1/4-20 or M6 Tapped Mounting Options
 - Black Anodized Aluminum Construction
- TECHSPEC® C, S, and T-Mount Ring Mounts feature a screw closure and accept 30mm, 16mm, and 48mm outer diameter tubes and barrels, respectively. Ring mounts are available with either 1/4-20 or M6 tapped mounting threads. TECHSPEC C, S, and T-Mount Ring Mounts are ideal for quickly integrating C, S, or T-Mount tube assemblies into any benchtop system. A black anodized construction reduces reflections within a system.

Technical Information

