

## Tip Kit, 8 piece Dissipative Straight



Representative Picture of Straight and Bent Probes

Stock **#57-646** **8 In Stock**

- 1 + C\$72<sup>10</sup>

**ADD TO CART**

### Volume Pricing

Qty 1+	C\$72.10 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### General

**Contents of Kit:**

8 straight probes: 3/32", 1/8", 3/16", 1/4", 3/8", 1/2", 5/8", 3/4"

### Regulatory Compliance

**Compliant**

Reach 191:

**Compliant**

RoHS 2015:

Certificate of Conformance:

## Product Details

- ESD-Safe
- Pen and Bulb Options
- General-Purpose Component Handling

Handi-Vac® and Pen-Vac® Pick-up Tool Kits feature lightweight, economical tools with black dissipative plastic handles and are available with non-marring static dissipative or conductive silicon vacuum cups. Placement accuracy is not as precise as a pen-style pick-up tool, but the bulb-style model is cost-effective enough to include in every tool kit. Simply squeeze the Handi-Vac® handle (bladder) for suction or press/release the Pen-Vac® push button to control the vacuum. Handi-Vac® and Pen-Vac® Pick-up Tool Kits have probes with stainless steel stems with zinc fittings. Black cups have a 0.035" inner diameter on the component side and can be directly mounted to the handle.

Handi-Vac® Kits include 4 interchangeable tips (OD cup size): 1/8" (one bent & one straight probe), 1/4" with bent probe, and 3/8" with straight probe. Pen-Vac® Kits include 6 tips, in the same sizes, each with one bent and one straight probe.

Tip Kits come with 8 straight probes: 3/32", 1/8", 3/16", 1/4", 3/8", 1/2", 5/8", 3/4" (OD cup size)

---