

Vis M62 x 0.75 Mounted Machine Vision Filter



Mounted Machine Vision Filters

Stock **#21-625** ☒ In Stock

-

1

+

C\$338.80

ADD TO CART

Qty 1-9

C\$338.80

Qty 10+

C\$321.44

Volume Pricing

[Request Quote](#)

Get Product Downloads

Blocking Wavelength Range (nm):

363 -380, 720-1100

Clear Aperture CA (mm):

57.10

Coating:

Hard Coated

Filter Thread:

M62 x 0.75
Color: Vis
Center Wavelength CWL (nm): 550.00
Construction: Mounted in Black Anodized Ring
Full Width-Half Max FWHM (nm): 300.00
Mount Thickness (mm): 5.2
Mount Thickness Including Threads (mm): 7.0
Outer Diameter (mm): 64.00
Substrate Thickness (mm): 1.3
Type: Mounted Imaging Filter
Minimum Transmission (%): ≥85

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View