

TECHSPEC® VIS-NIR 400 - 1100nm, 25mm Dia. Shortpass Filter Kit (29 Filters)



Stock **#86-463** [CONTACT US](#)

- 1 + **C\$8,610.00**

ADD TO CART

Qty 1+
C\$8,610.00

Volume Pricing
Request Quote

Get Product Downloads

Diameter (mm):
25.00

Optical Density OD (Average):
≥4.0

Substrate: ☐
[Fused Silica](#) (Corning 7980)

Filters Included :
Cut-Off Wavelength: [400nm](#) , [425nm](#), [450nm](#), [475nm](#),
[500nm](#), [525nm](#), [550nm](#), [575nm](#), [600nm](#), [625nm](#),
[650nm](#), [675nm](#), [700nm](#), [725nm](#), [750nm](#), [775nm](#),
[800nm](#), [825nm](#), [850nm](#), [875nm](#), [900nm](#), [925nm](#),
[950nm](#), [975nm](#), [1000nm](#), [1025nm](#), [1050nm](#), [1075nm](#),

[1100nm](#)

Coating:

Hard Coated

Transmission (%):

≥91

Type:

Shortpass Filter

Number of Filters:

29.00

Coating Specification:

Surface 1: Hard Dielectric Sputtered

Surface 2: MgF₂

Wavelength Range (nm):

300 - 1530

Regulatory Compliance

RoHS:

Not Compliant

Certificate of Conformance:

[View](#)