

VZM™ 1000 Zoom Imaging Lens



Stock **#54-396** ☐ In Stock

- 1 +

C\$1,617.00

ADD TO CART

Qty 1+

C\$1,617.00

Volume Pricing

[Request Quote](#)

Get Product Downloads

Length excluding Threads (mm):
248.10

Horizontal Field of View, 1/2" Sensor:
2.56 - 0.64mm

Horizontal Field of View, 2/3" Sensor:
3.52 - 0.88mm

Filter Thread:
None

Maximum Diameter (mm): 56.00
Weight (g): 770.00
Working Distance Tolerance (mm): ±1
Resolution, Object Space: 102.5 - 228 lp/mm
Resolution, Image Space: 41 - 22.8 lp/mm
Zoom Ratio: 4:1
Type: Zoom Lens
Primary Magnification PMAQ: 2.5X - 10X
Maximum Sensor Format: 2/3"
Working Distance (mm): 35.00
Mount: C-Mount
Lens Wavelength Range: VIS

Regulatory Compliance

RoHS: Exempt
Certificate of Conformance: View