

VZM™ 200i Zoom Imaging Lens



VZM™ 200i

Stock **#54-715** ☐ In Stock

1

C\$1,652.00

ADD TO CART

Qty 1+
C\$1,652.00

Volume Pricing
Request Quote

Get Product Downloads

Length excluding Threads (mm):
151.70

Horizontal Field of View, 1/2" Sensor:
12.0 - 3.0mm

Horizontal Field of View, 2/3" Sensor:
17.00 - 4.2mm

Filter Thread:
M22.5 x 0.50

Maximum Diameter (mm):
30.00

Weight (g): 232.00
Working Distance Tolerance (mm): ±3
Resolution, Object Space: 26 - 88 lp/mm
Resolution, Image Space: 52 - 44 lp/mm
Zoom Ratio: 4:1
Type: Zoom Lens
Primary Magnification PMAG: 0.5X - 2X
Maximum Sensor Format: 2/3"
Working Distance (mm): 90.00
Mount: C-Mount
Lens Wavelength Range: VIS

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View
