

VZM™ 600i Zoom Imaging Lens



VZM™ 600i

Stock #88-399 ☒ In Stock

1

C\$1,568.00

ADD TO CART

Qty 1+
C\$1,568.00
Volume Pricing
Request Quote

Get Product Downloads

Length excluding Threads (mm):
148.05

Horizontal Field of View, 1/2" Sensor:
6.4 - 1.0mm

Horizontal Field of View, 2/3" Sensor:
8.8 - 1.4mm

Filter Thread:
M22.5 x 0.50

Maximum Diameter (mm):
30.00

Weight (g): 250.00
Working Distance Tolerance (mm): ±3
Resolution, Object Space: 87 lp/mm - 176 lp/mm
Resolution, Image Space: 87 lp/mm - 29 lp/mm
Zoom Ratio: 6:1
Type: Zoom Lens
Primary Magnification PMAG: 1.0X - 6.0X
Maximum Sensor Format: 2/3"
Working Distance (mm): 60.00
Mount: C-Mount
Lens Wavelength Range: VIS

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
