

## White 150mm Compact Light w/ Dual OverDrive™



150mm Compact Light



Stock **#23-943** **1 In Stock**

⊖ 1 ⊕ C\$994<sup>00</sup>

**ADD TO CART**

### Volume Pricing

Qty 1+	C\$994.00 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### General

JWL150-DO-WHI **Model Number:**

LED Illuminator **Type of Illumination:**

Smart Vision Lights LLC **Manufacturer:**

Ring Light **Geometry:**

Constant or Strobed **Illumination Mode:**

## Physical & Mechanical Properties

**Dimensions (mm):**  
158.75 W x 84.25 H x 40.18 D (58.15 D Including Connector)

589.67 **Weight (g):**

65.38W x 65.38W **Active Area (mm):**

## Optical Properties

White **Color:**

500 - 2,000 **Working Distance (mm):**

## Electrical

10 - 7,000 **Strobe Duration (µs):**

## Hardware & Interface Connectivity

5-pin M12 connector **Connector:**

24 VDC ± 5% **Input Voltage (V):**

## Threading & Mounting

T-Slot for M6 Nut **Mount:**

## Environmental & Durability Factors

-10° to +40° **Operating Temperature (°C):**

IP65 **Environmental Rating:**

## Regulatory Compliance

[View](#) **Certificate of Conformance:**

## Product Details

- Utilize Dual OverDrive™ Technology for 10x Standard Light Output
- Offer Illumination Coverage over a Larger Field of View
- Direct Connect and Control via Camera's Trigger Output
- Ideal for High Speed Logistics Applications

Smart Vision Lights High Output Ring Lights are IP65-rated brightfield lights featuring a working distance of 500-mm to 2000-mm that can be directly connected to a camera for control via the trigger output. Built-in Dual OverDrive™ technology, which delivers up to 6 times the continuous power with a low-latency response and fast strobe durations down to 10ms. These lights feature a batwing design that illuminates a larger area than built-in lighting systems and produces a greater light output making them ideal to use alongside polarizers, diffusers, and other optical elements that reduce light output. Smart Visions Lights Illumination products offer an industry-leading 10-year limited warranty.