

White 200 x 200 High Power LED Backlight



Effilux High Power LED Backlights

Stock **#22-098** **3 In Stock**

⊖ 1 ⊕ C\$1,190.⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	C\$1,190.00 each
Need More?	Request Quote

Note: This item requires accessories for use | [Learn More](#)

Product Downloads

General

LED illumination	Type of Illumination:
>90%	Uniformity (%):
Effilux	Manufacturer:
Backlight	Geometry:

Illumination Mode:

Continuous with AIC (Analog Intensity Control)

Physical & Mechanical Properties**Dimensions (mm):**

239 x239

Weight (g):

1900

Active Area (mm):

200 x200

Optical Properties**Color:**

White

Hardware & Interface Connectivity**Power Supply:**

Power Supply Required and Sold Separately.

USA: [#15-874](#)Europe: [#15-875](#)Japan: [#73-409](#)Korea: [#73-409](#)China: [#15-874](#)**Environmental & Durability Factors****Operating Temperature (°C):**

0 - 50

Regulatory Compliance**RoHS 2015:**[Compliant](#)**Reach 224:**[Compliant](#)**Certificate of Conformance:**[View](#)**Product Details**

- >90% Uniformity
- Integrated Analog Controller for Precise Intensity and Dimming
- Anti-Reflection System to Absorb Stray Light

Effilux High Power LED Backlights offer high intensity, greater than 90% uniformity, and exceptional contrast providing a superior solution for backlight inspections. The convenient integrated analog controller allows precise control of power and intensity without the need for additional components. Effilux High Power LED Backlights feature an anti-reflection design which absorbs unwanted light to provide higher contrast to ensure a clear image. These backlights are ideal for machine vision inspection applications.

Note: Optional collimation film kits for 200 x200 backlights ([#22-104](#)) and 300 x300 backlights ([#22-105](#)) available and sold separately.