

White, 6.0" LED Line Light

See More by [Advanced Illumination](#)



Stock **#66-826** [CONTACT US](#)

- 1 +

C\$1,043.00

ADD TO CART

Qty 1+

C\$1,043.00

Volume Pricing

[Request Quote](#)

Note: This item requires accessories for use | [Learn More](#)

Get Product Downloads

Color:

White

Model Number:

LL3024A-WHI-IC

Mount:

Via (2) M2 Screws

Operating Temperature (°C):

0 to 65

Dimensions (mm): 174 L x 61 W x 24 D
Working Distance (mm): 25.4
LED Lifetime (hours): 100,000
Power Supply: Power Supply Required and Sold Separately. USA: #66-855 Europe: #66-855 Japan: #66-855 Korea: #33-773 China: #66-855
Light Distribution (%): ±5 Over Illuminated Area (Dependent on Working Distance)
Number of LEDs: 24.00
Number of Channels: 1.00
Field Coverage (mm): 6.35 thick
Maximum Trigger Frequency (Hz): 30.00
Strobe Duration (µs): 30 - 300
Type of Illumination: LED Illuminator
Note: Optional Manual Intensity Adjustment #86-887 and #89-555 are Available
Manufacturer: Advanced Illumination
Geometry: Line Light
Illumination Mode: Constant

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Contains SVHC(s)