print-screen-header

English CAD Contact Us

SCHOTT KG1, 50mm Dia., 3mm Thick, Colored Glass Heat Absorbing Shortpass Filter

See More by SCHOTT Optical Components



Stock **#45-648** In Stock

- 1 + **C$112.00**

ADD TO CART

Qty 1-10
C$112.00

Qty 11+
C$98.00

Volume Pricing
Request Quote

Get Product Downloads

Diameter (mm):
50.00

Density (g/cm^3):
2.53

Glass/Filter Number:
SCHOTT KG1

Substrate:
Heat Absorbing Glass

Operating Temperature (°C):
300 Maximum

Coating:
Uncoated

Index of Refraction n_d:
1.51

Surface Quality:
60-40

Transformation Temperature (°C):
599

Thickness (mm):
3.00 ±0.38

Type:
IR Cut-Off Filter

Dimensional Tolerance (mm):
±0.25

Reflection Factor P_d:
0.92

Wavelength Range (nm):
300 - 2700

Bevel:
Protective as needed

Regulatory Compliance

RoHS 2015:
Compliant

Certificate of Conformance:
View