print-screen-header

Hoya UV28N (280nm), 50.8mm Sq., 1mm Thick, Colored Glass Longpass Filter

See More by Hoya



Stock **#18-797** In Stock

- 1 + **C$123.20**

ADD TO CART

Qty 1-10
C$123.20

Qty 11+
C$109.20

Volume Pricing
Request Quote

Get Product Downloads

CUSTOM OPTIONS

Dimensions (mm):	50.8 x 50.8
Cut-On Wavelength (nm):	280.00 ±7
Density (g/cm^3):	2.61

Glass/Filter Number:
Hoya UV28N

Substrate:
Colored Glass

Coating:
Uncoated

Color:
Clear

Surface Quality:
60-40

Transformation Temperature (°C):
572

Thickness (mm):
1.00

Thickness Tolerance (mm):
±0.1

Type:
Longpass Filter

Wavelength:
UV

Dimensional Tolerance (mm):
±0.2

Reflection Factor P_d:
0.92

Bevel:
Protective as needed

Δλ (nm):
<45

TH (%):
>85

Regulatory Compliance

RoHS:
Compliant

Certificate of Conformance:
View