

[All Products](#) / [Cameras](#) / [USB Cameras](#)

JAI GO-X Cameras



- Up to 12.3 MP Resolution
- USB and GigE Versions Available
- Longest Industry Warranty (6 Years)

Common Specifications

General

Manufacturer: JAI

Camera Series: Go-X

Physical & Mechanical Properties

Dimensions (mm): 29 x 29 x 51.5

Weight (g): 65

Housing: Full

Sensor

Pixel Size, H x V (μm): 3.45 x 3.45

Type of Sensor: Progressive Scan CMOS

Shutter Type: Global

Pixel Depth: 8/10/12 Bit

Hardware & Interface Connectivity

Power Supply: Power Supply Required
and Sold Separately:
USA: #29-171
Europe: #29-171
Japan: #29-171
Korea: Not Available
China: Not Available

Synchronization: Hardware Trigger (GPIO)
or Software Trigger

**Interface Port
Orientation:** Back Panel

GPIO Connector Type: 6-pin Hirose

Threading & Mounting

Mount: C-Mount

Environmental & Durability Factors

**Operating Temperature
(°C):** -5 to +45

**Storage Temperature
(°C):** -25 to +60

Technical Information

Products

Title	Stock Number	Price	Buy
JAI Go-X, 2402M-PGE, 1/2.3" 2.3MP, GigE Monochrome Camera	#29-146	C\$924.63	1 In Stock
JAI Go-X, 2402C-PGE, 1/2.3" 2.3MP, GigE Color Camera	#29-147	C\$924.63	1 In Stock
JAI Go-X, 5103M-PGE, 2/3" 5.01 MP, GigE Monochrome Camera	#29-148	C\$1,344.21	1 In Stock
JAI Go-X, 5103C-PGE, 2/3" 5.01 MP, GigE Color Camera	#29-149	C\$1,344.21	2 In Stock
JAI Go-X, 8901M-PGE, 1" 8.9MP, GigE Monochrome Camera	#29-150	C\$2,587.41	1 In Stock
JAI Go-X, 8901C-PGE, 1" 8.9MP, GigE Color Camera	#29-151	C\$2,587.41	1 In Stock
JAI Go-X, 12401M-PGE, 1.1" 12.3MP, GigE Monochrome Camera	#29-152	C\$3,170.16	1 In Stock
JAI Go-X, 12401M-PGE, 1.1" 12.3MP, GigE Color Camera	#29-153	C\$3,170.16	1 In Stock
JAI Go-X, 2402M-USB, 1/2.3" 2.3MP, USB Monochrome Camera	#29-154	C\$1,080.03	1 In Stock
JAI Go-X, 2402C-USB, 1/2.3" 2.3MP, USB Color Camera	#29-155	C\$1,080.03	1 In Stock
JAI Go-X, 5103M-USB, 2/3" 5.01 MP, USB Monochrome Camera	#29-156	C\$1,499.61	1 In Stock
JAI Go-X, 5103C-USB, 2/3" 5.01 MP, USB Color Camera	#29-157	C\$1,499.61	1 In Stock
JAI Go-X, 8901M-USB, 1" 8.9MP, USB Monochrome Camera	#29-158	C\$2,618.49	1 In Stock
JAI Go-X, 8901C-USB, 1" 8.9MP, USB Color Camera	#29-159	C\$2,618.49	1 In Stock
JAI Go-X, 12401M-USB, 1.1" 12.3MP, USB Monochrome Camera	#29-160	C\$3,232.32	1 In Stock
JAI Go-X, 12401M-USB, 1.1" 12.3MP, USB Color Camera	#29-161	C\$3,232.32	1 In Stock



Copyright 2023, Edmund Optics Inc., 101 East Gloucester Pike, Barrington, NJ 08007-1380 USA

Phone: 1-800-363-1992 :

www.edmundoptics.com