

[See all 13 Products in Family](#)

TECHSPEC®

S-Mount, 12.5mm x 17.6mm Plate Mount



Plate S-Mount Holder (#11-142)

Stock **#11-142** 2 In Stock

-

1

+

C\$389<sup>20</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-4        | C\$389.20 each                |
| Qty 5-9        | C\$364.00 each                |
| Qty 10-25      | C\$346.36 each                |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

General

Function:

Optic Mount (Fixed)

Type of Optics:

Rectangular

Note:

Includes one S-Mount Aperture Cap ([# 11-137](#))

Dimensions of Compatible Optics (mm):

12.5 x 17.6

| Physical & Mechanical Properties |                                           |
|----------------------------------|-------------------------------------------|
| 30.0 x 30.0 x 28.5               | Dimensions (mm):                          |
| 30.0                             | Extension Length (mm):                    |
| 1.0                              | Min. Thickness of Compatible Optics (mm): |
| 3.0                              | Max. Thickness of Compatible Optics (mm): |
| Threading & Mounting             |                                           |
| S-Mount                          | Thread Type:                              |
| 1/4-20                           | Compatible Post:                          |
| Regulatory Compliance            |                                           |
| Compliant                        | RoHS 2015:                                |
| View                             | Certificate of Conformance:               |

## Product Details

- C, S, and T-Mount Solutions for Mounting Cube and Plate Beamsplitters, Filters, and Mirrors
  - Provides a 90° Mounting Interface
  - 1/4-20 and M6 Tapped Mounting Threads for English or Metric Based Systems
- TECHSPEC® C, S, and T-Mount Cube and Plate Mounts allow for the integration of cube and plate optics into C, S, and T-Mount systems. These mounts feature four C, S, or T-Mount threaded apertures that can also act as connection points for other C, S, or T-Mount components. Either an M6 or 1/4-20 tapped hole is provided on the base for post mounting, making these mounts compatible with breadboard and benchtop systems. TECHSPEC C, S, and T-Mount Cube and Plate Mounts provide a 90° mounting interface ideal for placing beamsplitters, filters, and mirrors within a system. C, S, and T-Mount Aperture Caps are available to block light from unused openings and to protect the optic from dust and debris.
- Note:** [#11-139](#) and [#11-142](#) each include one S-Mount Aperture Cap ([#11-137](#))

## Technical Information

