

TECHSPEC® 25mm SM05 Lens Tube



TECHSPEC® ID Lens Tubes

Stock #35-779 **20+ In Stock**

1 C\$18^{.20}

ADD TO CART

Volume Pricing	
Qty 1-5	C\$18.20 each
Qty 6-25	C\$16.52 each
Qty 26+	C\$15.96 each
Need More?	Request Quote

Product Downloads	
STEP:step	PDF Drawing:pdf
IGES:igs	eDrawing:eprt
EO Spec Sheet	Download All

General

Type: Extension Tube	Function: Extension Tube (Fixed)
-----------------------------	---

Physical & Mechanical Properties

Extension Length (mm): 25.0	Clear Aperture CA (mm): 10.0
Construction: Anodized Aluminum	Outer Diameter (mm): 16.0

Threading & Mounting

Thread Type: 0.535 x 40 TPI (SM05)

Regulatory Compliance

RoHS 2015: Compliant	Certificate of Conformance: View
REACH 241: Compliant	

Product Details

- Enables Mounting for 25/25.4mm and 12.5/12.7mm Optics
- Ideal for Optical System Creation and Integration
- Continuous SM1 or SM05 Barrel Thread for Mounting Multiple Components

The TECHSPEC® SM Lens Tubes offer an efficient method for mounting single or multiple optical components. Featuring anodized aluminum construction for a light-weight mounting solution, these lens tubes include a barrel thread that extends through the barrel for continuous lens mounting space. The TECHSPEC SM Lens Tubes utilize SM1 (1.035" x 40 TPI) or SM05 (0.535" x 40 TPI) threads and are ideal for integration with [TECHSPEC Plano-Convex](#) and [TECHSPEC Achromatic Lenses](#).

Note: Retainer ring sold separately. Spanner wrench [#11-046](#) has a specialized wrench head on one end designed for SM Tube System retainer ring adjustment.

Accessories

Note: Compatible accessories for individual stock numbers may vary. If unsure about which accessories work with your products, please contact us [here](#).

	Title	Compare	Stock Number	Price	Buy
MORE+	SM1 Retainer Ring		#35-763	C\$7.35 Request Quote	20+ In Stock <input type="text" value="1"/>
MORE+	SM05 Retainer Ring		#35-784	C\$7.35 Request Quote	20+ In Stock <input type="text" value="1"/>
MORE+	Multi-Element Tube Spanner Wrench		#11-046	C\$79.80 Request Quote	20+ In Stock <input type="text" value="1"/>
MORE+	SM1 Tube, 5mm Optic Adapter		#36-435	C\$42.00 Volume Pricing Request Quote	20+ In Stock <input type="text" value="1"/>
MORE+	SM1 Tube, 6mm Optic Adapter		#36-434	C\$42.00 Volume Pricing Request Quote	20+ In Stock <input type="text" value="1"/>
MORE+	SM1 Tube, 9mm Optic Adapter		#36-432	C\$42.00 Volume Pricing Request Quote	20+ In Stock <input type="text" value="1"/>
MORE+	SM1 Tube, 10mm Optic Adapter		#36-422	C\$42.00 Volume Pricing Request Quote	13 In Stock <input type="text" value="1"/>
MORE+	SM1 Tube, 15mm Optic Adapter		#36-421	C\$42.00 Volume Pricing Request Quote	20+ In Stock <input type="text" value="1"/>
MORE+	SM1 Tube, 18mm Optic Adapter		#36-420	C\$42.00 Volume Pricing Request Quote	15 In Stock <input type="text" value="1"/>
MORE+	SM1 Tube, 19.05mm Optic Adapter		#36-419	C\$42.00 Volume Pricing Request Quote	20+ In Stock <input type="text" value="1"/>

Related Products



#11-046 - Multi-Element Tube Spanner Wrench
C\$79.80



SM Brass Spacer Rings



SM Lens Tube Drop-In Mounts



Multi-Element Outer Tubes

Frequently Purchased Together



#03-618 - 5mm Spacer to convert CS-Mount Cameras to C-Mount
C\$40.60

Qty




#03-629 - C-Mount Double Male Thread Ring
C\$51.45

Qty



#03-630 - C-Mount Double Female Thread Ring
C\$51.45

Qty



#32-945 - 25mm Dia Enhanced Aluminum, 4-6λ Mirror
C\$43.40

Qty



Resources

Media Type

Glossary

GLOSSARY

Bezel

GLOSSARY

Normal Load Capacity

GLOSSARY

Roll

GLOSSARY

Yaw

GLOSSARY

C-Mount