

## Coarse/Fine Movement, 50mm Dia Thru w/ Rotation, Rack & Pinion



#59-321

Stock **#59-321** 6 In Stock

-

1

+

C\$903<sup>00</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1+         | C\$903.00 each                |
| Need More?     | <a href="#">Request Quote</a> |

| Product Downloads |
|-------------------|
|-------------------|

| General                  |                     |
|--------------------------|---------------------|
| Rack and Pinion Mount    | Type:               |
| 50 mm Diameter Thru-Hole | Note:               |
| Coarse/Fine Movement     | Type of Adjustment: |

| Physical & Mechanical Properties                                  |  |
|-------------------------------------------------------------------|--|
| Dimensions (mm):<br>Rack and Pinion Block: 50.8 H x28.6 W x50.8 L |  |

|                       |                                    |
|-----------------------|------------------------------------|
| 35 (+23/-12) in Y     | Travel (mm):                       |
| 1.31                  | Weight (lbs):                      |
| 25.5 coarse, 3.2 fine | Travel Per Knob Rotation (mm):     |
| 2.00                  | Load Capacity (kg):                |
| Linear (Y), Rotation  | Type of Movement:                  |
| 100.00                | Optical Centerline from Post (mm): |

Threading & Mounting

|                                          |                                |
|------------------------------------------|--------------------------------|
| 3/4" Diameter Post<br>1/4-20 Tapped Hole | Mounting Post Hole and Thread: |
|------------------------------------------|--------------------------------|

Regulatory Compliance

|                  |                             |
|------------------|-----------------------------|
| Exempt           | RoHS 2015:                  |
| Contains SVHC(s) | Reach 224:                  |
| View             | Certificate of Conformance: |

## Product Details

- Coarse or Fine Motion Available
- Thru Holes for Integrating Lenses
- 1/4-20 Stud for Mounting Cameras
- Imaging System Bases, Stainless Steel Posts, and Accessories also Available

Rack and Pinion Focusing Mounts for Imaging Systems add additional focus ability to imaging systems. Thru Holes are ideal for use with [TECHSPEC® VZM™ Zoom Imaging Lenses](#) or other imaging lenses. Rack and Pinion Movement with 1/4-20 stud can be used with any compatible camera or imaging lens. Rack and Pinion Focusing Mounts for Imaging Systems are offered with either coarse or fine motion.[Imaging System Bases, Stainless Steel Posts](#), and [Accessories](#) are also available.