

[See all 105 Products in Family](#)

IDS U3-38C4XLS-C-HQ, USB 3.0, 1/2.8" Color Board Level Camera

See More by [IDS Imaging Development Systems](#)



Stock #78-280 [CONTACT US](#)

1 **C\$319²⁰**

ADD TO CART

Volume Pricing	
Qty 1+	C\$319.20 each
Need More?	Request Quote

Product Downloads

Color **Spectrum:**

General

Color Camera **Type:**

U3-38C4XLS-C-HQ **Model Number:**

IDS Imaging Development Systems **Manufacturer:**

uEye+ XLS

Camera Series:

Physical & Mechanical Properties

Dimensions (mm):

32.5 x 32.5 x 14 (excludes connectors and lens mount)

Weight (g):

15

Housing:

Board Level

Sensor

Image Buffer:

Not Specified

Sensor Format:

1/2.8"

Resolution (Megapixels):

2.16

Frame Rate (fps):

88.00

Pixels (H x V):

1,936 x 1,096

Pixel Size, H x V (µm):

2.90 x 2.90

Sensing Area, H x V (mm):

5.614 x 3.178

Imaging Sensor:

Sony IMX662

Type of Sensor:

Progressive Scan CMOS

Shutter Type:

Rolling

Pixel Depth:

12 bit

Exposure Time:

0.009ms - 2000ms

Dynamic Range (dB):

74.00

Machine Vision Standard:

USB3 Vision

Electrical

Power Consumption (W):

0.5 - 0.9

Hardware & Interface Connectivity

Interface:

USB 3.0

Connector:

USB 3.0 micro-B

Power Supply:

Power over USB

GPIO Connector Type:

8-pin connector

Threading & Mounting

Mount:

C/CS-Mount

Environmental & Durability Factors

Operating Temperature (°C):

0 to +75

Storage Temperature (°C):

-20 to +80

Regulatory Compliance

Certificate of Conformance:

[View](#)

Product Details

- Standard (SE), Compact (CP), and Ultra Compact (XCP) Housing Options Available
- C-Mount with Large Format CMOS Sensors up to 1.1"

- Up to 20.44MP Resolution with Framerrates up to 396fps

IDS Imaging uEye CP/XCP/SE USB3 Cameras utilize [IDS Imaging's peak SDK platform](#) that supports GeniCam and USB3 Vision standards for easy software development and integration. The CP cameras are the industry standard size of 29 x 29 x 29mm and work for almost any application. The XCP cameras have an ultra-compact size of 29 x 29 x 17mm and are an excellent option for price-sensitive, single-camera applications. The SE cameras have a larger housing size of 34 x 44 x 47mm to allow for exceptional heat management and are ideal for noise and heat-sensitive applications. IDS Imaging uEye CP/XCP/SE USB3 Cameras are ideal for manufacturing, industrial, and automation applications.

Calibration Services
