

[See all 105 Products in Family](#)

IDS U3-36P0XCP-C-HQ, USB 3.0, 1/1.8" Color Camera (Recertified 05-P)

See More by [IDS Imaging Development Systems](#)



IDS Imaging uEye+ USB3 Cameras



Stock **#78-258-RCD-05P** RECERTIFIED **1 In Stock**

⊖ 1 ⊕ C\$322⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	C\$322.00 each
Need More?	Request Quote

Product Downloads

Color	Spectrum:
-------	-----------

General

Color Camera	Type:
U3-36P0XCP-C-HQ	Model Number:
	Manufacturer:

uEye+ XCP **Camera Series:**

Physical & Mechanical Properties

Dimensions (mm):
29 x 29 x 17 (excludes connectors and lens mount)

Weight (g):
60

Housing:
Full

Sensor

Image Buffer:
Not Specified

Sensor Format:
1/1.8"

Resolution (Megapixels):
19.80

Frame Rate (fps):
15.00

Pixels (H x V):
5,120 x 3,840

Pixel Size, H x V (µm):
1.40 x 1.40

Sensing Area, H x V (mm):
7.168 x 5.376

Imaging Sensor:
ON Semi AR2020

Type of Sensor:
Progressive Scan CMOS

Shutter Type:
Rolling

Pixel Depth:
10 bit

Exposure Time:
0.035ms - 2000ms

Dynamic Range (dB):
63.00

Machine Vision Standard:
USB3 Vision

Electrical

Power Consumption (W):
0.5 - 1.1

Hardware & Interface Connectivity

Interface:
USB 3.0

Connector:
USB 3.0 micro-B, screwable

Power Supply:
Power over USB

GPIO Connector Type:
8-pin connector

Threading & Mounting

Mount:
C-Mount

Environmental & Durability Factors

Operating Temperature (°C):
0 to +55

Storage Temperature (°C):
-20 to +60

Regulatory Compliance

Certificate of Conformance:
[View](#)

Product Details

- Standard (SE), Compact (CP), and Ultra Compact (XCP) Housing Options Available

- C-Mount with Large Format CMOS Sensors up to 1.1"
- Up to 20.44MP Resolution with Framerrates up to 396fps

IDS Imaging uEye CP/XCP/SE USB3 Cameras utilize [IDS Imaging's peak SDK platform](#) that supports GeniCam and USB3 Vision standards for easy software development and integration. The CP cameras are the industry standard size of 29 x 29 x 29mm and work for almost any application. The XCP cameras have an ultra-compact size of 29 x 29 x 17mm and are an excellent option for price-sensitive, single-camera applications. The SE cameras have a larger housing size of 34 x 44 x 47mm to allow for exceptional heat management and are ideal for noise and heat-sensitive applications. IDS Imaging uEye CP/XCP/SE USB3 Cameras are ideal for manufacturing, industrial, and automation applications.

Calibration Services
