

[See all 23 Products in Family](#)

InfiniTube FM-200 with InLine Attachment for +10X Objectives

See More by [Infinity Photo-Optical Company](#)



InfiniTube FM-200 (1X), #58-310



Stock **#58-311** **2 In Stock**

C\$2,345⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	C\$2,345.00 each
Need More?	Request Quote

Product Downloads

General

Fixed Magnification Lens **Type:**

In-Line Illumination **Type of Illumination:**

Optical Properties

Objective Required **Primary Magnification PMAG:**

Sensor

2/3" **Maximum Sensor Format:**

Threading & Mounting

C-Mount **Mount:**

Regulatory Compliance

Compliant **RoHS 2015:**

Compliant **Reach 224:**

View **Certificate of Conformance:**


Product Details

- Direct to Video C-Mount for 2/3" and Smaller Sensor Cameras
- Internal Focusing

InfiniTube™ FM Systems are used to mount infinite-conjugate objectives to C-mount cameras, yielding magnifications not possible with ordinary video lenses, such as 50X magnification. The InfiniTube™ system can be configured in a variety of fashions. It can be utilized alone (InfiniTube™ #58-310 or #58-309) for applications where illumination is provided from another source such as a backlight or directional illumination. The InfiniTube™ FM Systems can also be configured for in-line illumination with attachments. The first in-line attachment (#58-313) has been designed for high performance with objectives having a magnification of 10X or below and is not suggested for use with higher magnification objectives. The second in-line attachment (#58-312) has been designed to work with increased efficiency when used with magnifications of 10X or higher, but can be utilized with all magnifications. All in-line attachments accept our **Fiber Optic Light Guides** with a 0.312" tip diameter.

Note: **Standard system** for 2/3" sensors still available.

Technical Information



Note:
The PL-Series Objectives are specifically designed to be used directly (no adapters required) with the InfiniTube™ FM-Series Main Bodies.

All PL-Series Objectives are amplified by 2X (InfiniTube FM-100) or 4X (InfiniTube™ FM-200) their engraved initial power ratings.

A DL 2X Tube can be used atop InfiniTube™ FM-Series Main Bodies to further amplify magnification by a 2X factor.

System Includes	Stock No.
InfiniTube In-Line Assembly Unit	#58-311
Hitachi KP-D20B Camera	#55-837
15.1" Diagonal LCD Monitor (US version only)	#56-522
Y-C Cable (6 ft.)	#39-255
Mitutoyo/Achrovid™ Objective Adapter	#58-316
M-150 Fiber Optic Illuminator	#55-718
Fiber Optic Light Guide (48" L)	#39-367
Fiber Optic Adapter	#38-944
Standard Boom Stand	#54-120
Rack & Pinion Mounting Plate	#54-123
C-Clamp with 1/4-20 Mounting Hole	#57-788