

[See all 7 Products in Family](#)

# Leica N Plan 50x Objective

See More by [Leica](#)



Leica Achromatic N Plan Objectives

Stock **#29-535** 5 In Stock

-

1

+

C\$3,038<sup>.00</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1+         | C\$3,038.00 each              |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

| General                                                        |              |
|----------------------------------------------------------------|--------------|
| Compatible Tube Lens Focal Length (mm):<br>Focal Length: 200mm |              |
| Infinity Corrected                                             | Style:       |
| Leica                                                          |              |
| Manufacturer:                                                  |              |
| Physical & Mechanical Properties                               |              |
| 49.40                                                          | Length (mm): |

|                       |                                        |
|-----------------------|----------------------------------------|
| 29                    | Maximum Diameter (mm):                 |
| 2.8                   | Exit Pupil Diameter (mm):              |
| Optical Properties    |                                        |
| 0.17                  | Compatible Cover Glass Thickness (mm): |
| 4.00                  | Focal Length FL (mm):                  |
| 50X                   | Magnification:                         |
| 0.75                  | Numerical Aperture NA:                 |
| 0.36                  | Resolving Power (μm):                  |
| 0.32                  | Depth of Field (μm):                   |
| 0.37                  | Working Distance (mm):                 |
| 22                    | Field Number (mm):                     |
| 45.0                  | Parfocal Length (mm):                  |
| Dry                   | Immersion Liquid:                      |
| Threading & Mounting  |                                        |
| M25 x0.75             | Mounting Threads:                      |
| Regulatory Compliance |                                        |
| <a href="#">View</a>  | Certificate of Conformance:            |

## Product Details

- Excellent Color Correction and Flatness of Field
- 5X to 100X Magnifications Available
- Designed for Transmitted Light and DIC Illumination Techniques
- M25 x0.75 Threading
- Low-Cost Alternative, **Hi Plan** Objectives Available

Leica Achromatic N Plan Objectives are powerful objectives with improved color performance over the visible spectral range and offer excellent field flatness up to a 25mm field of view. These objectives are available in magnifications from 5X, 10X, 20X, 40X, 50X, and 100X. Leica Achromatic N Plan Objectives are designed for varying illumination techniques such as transmitted light and differential interference contrast (DIC). These objectives are ideal for life science and materials research, industrial quality control and failure analysis, and medical and surgical imaging applications.