


[See all 15 Products in Family](#)

Lumenera INFINITY 8-9C Microscopy Color Camera (Recertified 05-P)

See More by [Teledyne Lumenera](#)



Stock **#25-355-RCD-05P** RECERTIFIED **1 In Stock**

-

1

+

C\$7,000^{.00}

ADD TO CART

Volume Pricing	
Qty 1+	C\$7,000.00 each
Need More?	Request Quote

Product Downloads

Color		Spectrum:
General		
Color Microscopy Camera		Type:
i8-LC00-09M		Model Number:
Teledyne Lumenera		Manufacturer:

INFINITY		Camera Series:
Physical & Mechanical Properties		
Dimensions (mm):		41.5 x45 x45 (includes lens mount)
Weight (g):		108
Housing:		Full
Sensor		
Image Buffer:		128MB
Sensor Format:		1"
Resolution (Megapixels):		8.90
Frame Rate (fps):		31.00
Pixels (H x V):		4,112 x2,176
Pixel Size, H x V (µm):		3.45 x3.45
Sensing Area, H x V (mm):		14.19 x7.51
Imaging Sensor:		Sony IMX267
Type of Sensor:		Progressive Scan CMOS
Shutter Type:		Global
Pixel Depth:		8/12 bit
Dynamic Range (dB):		73.3
Electrical		
Power Consumption (W):		2.3 - 3.6
Hardware & Interface Connectivity		
Interface:		USB 3.1
Power Supply:		Power over USB
GPIOs:		Not Specified
Synchronization:		Hardware Trigger (GPIO)
Interface Port Orientation:		Side Panel
GPIO Connector Type:		9-pin Hirose (JST)
Threading & Mounting		
Mount:		C-Mount
Mounting Threads:		M3x0.5 (Integrated into Housing)
Environmental & Durability Factors		
Operating Temperature (°C):		0 to +50
Storage Temperature (°C):		-30 to +70
Regulatory Compliance		
Certificate of Conformance:		View

Product Details

- Exceptional Low Light Sensitivity
- Ideal for Life Sciences, Clinical, and Industrial Applications
- Affordable Price Point with Included Microscopy Software



Teledyne Lumenera INFINITY8 Microscopy Cameras offer an affordable solution for low light imaging in a compact form factor. Featuring low noise and large pixels, these cameras are ideal for a wide range of lighting conditions including the low light levels common in fluorescence imaging. Available with 1/1.8", 2/3", and 1" sensor sizes and megapixel range of 2 – 20 MP, each camera is compatible with Windows and Mac operating systems. Teledyne Lumenera INFINITY8 Microscopy Cameras include an INFINITY ANALYZE 7 software license, for camera operation and immediate analysis of the imaging results, and 3m Micro-B to Type-A USB cable.