

TECHSPEC<sup>®</sup> M43 x 0.75 Mount for 50/50.8mm Diameter Filters



M43 x 0.75 Mount for 50/50.8mm Diameter Filters, #12-789

Stock **#12-789** 20+ In Stock

-

1

+

C\$84<sup>00</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-9        | C\$84.00 each                 |
| Qty 10+        | C\$77.00 each                 |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

| Physical & Mechanical Properties  |                         |
|-----------------------------------|-------------------------|
| 40.0                              | Clear Aperture CA (mm): |
| 55.0                              | Outer Diameter (mm):    |
| 16.00                             | Thickness (mm):         |
| Black Anodized Aluminum (6061-T6) | Construction:           |

Threading & Mounting

|                                                        |                                      |
|--------------------------------------------------------|--------------------------------------|
| M43 x0.75                                              | Filter Thread:                       |
| M43.0 x0.75 / M52.5 x0.5 (Male Thread / Female Thread) | Mount:                               |
| 50.0 - 50.8                                            | Diameter of Compatible Optics (mm):  |
| 7.0 Maximum                                            | Thickness of Compatible Optics (mm): |

Regulatory Compliance

|           |                             |
|-----------|-----------------------------|
| Compliant | RoHS 2015:                  |
| View      | Certificate of Conformance: |
| Compliant | Reach 235:                  |

Product Details

- Specially Designed to Hold 25/25.4mm and 50/50.8mm Diameter Filters
  - Accommodate up to 7mm Thicknesses
  - Choose from our Full Selection of 25mm or 50mm Diameter Filters
  - [Premounted Edge Filters](#) and [Neutral Density Filters](#) Available
- TECHSPEC® Machine Vision Filter Mounts for 25 and 50mm Diameter Filters are designed to hold 25/25.4mm and 50/50.8mm diameter filters, enabling our full selection of [filters](#) to be used in imaging systems. Whether your application requires a unique bandpass, edge, notch, or neutral density filter, you can now easily attach any of our standard filter designs to the front of most imaging lenses. TECHSPEC® Machine Vision Filter Mounts for 25 and 50mm Diameter Filters have been designed to accommodate up to 7mm of filter thickness, making it easy to stack multiple [Hoya Absorptive Neutral Density Filters](#) to achieve custom optical densities. Even many of our [Hard Coated Bandpass Interference Filters](#) can now be easily integrated into imaging applications. These filters are constructed of black anodized aluminum and are available in various sizes of filter threads.
- [#65-800](#) is an ideal accessory to our family of [TECHSPEC® C Series Fixed Focal Length Lenses](#), and [#65-801](#) is an ideal accessory to the [Megapixel Fixed Focal Length Lenses](#) and [Schneider Compact VIS-NIR Lenses](#). The 50/50.8mm diameter filter mounts are ideal accessories for our large format imaging lenses, including our [1.1" HP Series Fixed Focal Length Lenses](#) and [TECHSPEC® LF Series Fixed Focal Length Lenses](#).