

Pedestal Post, Metric, 25.4mm



Pedestal Post

Stock **#15-840** [CONTACT US](#)

-

1

+

C\$24⁻¹³

~~€\$37.12~~

ADD TO CART

Volume Pricing	
Qty 1-4	€\$37.12 C\$24.13 each
Qty 5-9	€\$33.52 C\$21.79 each
Qty 10+	€\$32.93 C\$21.40 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

General

Metric

Type:


Note:

With M6x1.0 screw holes on the base	
Pedestal Post	Function:
Physical & Mechanical Properties	
0.09	Weight (kg):
Stainless Steel	Construction:
25.40	Length (mm):
25.4	Post Diameter (mm):
31.5	Base Diameter (mm):
Threading & Mounting	
M4x0.7	Mounting Threads:
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 247:

PRODUCT DETAILS

- 1" Diameter Posts with Metric and English Mounting Hole Options
 - Stainless Steel Construction for High Stability
 - 0.5"- 4.0" Heights Available
 - Refer to the Technical Information Tab to Find the Right Adapter for your Optical Mount and Application
- Pedestal Posts and Accessories offer a stable way to mount optical components to a lab table with a consistent mounting height, providing predictable and repeatable mounting of components within an optical system. A variety of pedestal extenders and shim plates are available to ensure that the optical axis height is consistent for all mounted components. Pedestal Posts feature M4 x 0.7 or 8-32 tapped holes on the top surface, compatible with [TECHSPEC® Kinematic Mounts](#), [E-Series Kinematic Mounts](#), [Compact Mirror Mounts](#), and many other [optical mounts](#). M6 x 1.0 or 1/4"-20 tapped holes on the bottom surface make these Pedestal Posts directly mountable to Edmund Optics [stages](#) and [breadboards](#). For more compact table mounting, use the Compact Mounting Clamps ([#16-335](#)).
- Note:** Optical Mount Adapters are available to ensure consistent optical axis height and mounting hole compatibility with Edmund Optics' Optical Mounts. Refer to the Technical Information tab to find the right adapter for your application.

TECHNICAL INFORMATION

PEDESTAL POSTS AND ACCESSORIES					
Compatible Optic Mount	Optical Size	Mount Stock Number	Exension Length (mm)	Extender Stock Number for English Pedestals	Extender Stock Number for Metric Pedestals
 Optic Component Mount	50mm Dia.	#64-567	16.8	#16-321	#16-315
	2"/50.8mm Dia.	#64-569	16.8	#16-324	#16-587
 Bar-Type Lens / Filter Holder	1"/25.4mm Dia	#03-676	18	#16-325	#16-588
	2 axis: 2"/50.8mm Dia.	#62-957	8	#16-317	#16-311
	3 axis: 1"/25.4mm Dia.	#62-959	18	#16-222	#16-316
	5 axis: 1"/25.4mm Dia.	#13-776	18	#16-222	#16-316
	2"/50.8mm Dia.	#03-669	11	#16-323	#16-586
	2"/50.8mm Dia.	#55-530	16	#16-320	#16-314
 Multi-Axis Adjustable Optic Mounts	2 axis: 1"/25.4mm Dia.	#62-956	20.8	#16-460	#16-459
					

 Rectangular Bar Clamp	2"/50.8mm Sq.	#54-995	11	#16-318	#16-312
 Filter Mount	2"/50.8mm Sq.	#54-997	14	#16-319	#16-313
 Multiple Filter Holder	30mm Dia.	#55-006	16	#16-320	#16-314
 Spring Mount Filter Holder	2"/50.8mm Sq.	#55-531	16	#16-320	#16-314
 Prism Mounts	25mm Cube	#55-013	18	#16-322	#16-316
	50mm Cube	#53-027	18	#16-325	#16-588
 Polarizer	1"/25.4mm Dia.	#55-011	18	#16-322	#16-316
	2"/50.8mm Dia.	#56-329	8	#16-317	#16-311
 Top Adjustment Kinematic Mount	1"/25.4mm Dia.	#55-456	14	#16-319	#16-313
 Gimbal Mount	2"/50.8mm Dia.	#55-000	11	#16-318	#16-312