

NOTES:


1. SUBSTRATE MATERIAL:  
N-BK7
2. COATING (APPLY ACROSS CLEAR APERTURE)

S1 & S2:  
LASER V-COAT

R(abs) <0.25% @ 405nm  
R(avg) <1.5% @ 375 - 435nm



3. FINE GROUND SURFACE

4. POWER, IRREGULARITY, AND SURFACE QUALITY  
SPECIFICAIONS APPLY ACROSS CLEAR APERTURE
5. RoHS COMPLIANT



**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

REV. A	S1	S2					
SHAPE	CONVEX	PLANO	EFL	75±3%	 Edmund Optics®		
RADIUS	38.89	∞	BFL	(72.89)			
SURFACE QUALITY	60-40	60-40			TITLE	25.0mm DIA X 75.0mm FL 405nm V-COAT, CYLINDER LENS	
CLEAR APERTURE	Ø 24.00	Ø 24.00					
COATING APERTURE	Ø 24.00	Ø 24.00					
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED	ALL DIMS IN	mm	DWG NO	33221	SHEET 1 OF 1