



NOTES:


1. SUBSTRATE:
LOW DISPERSION POLYMER
2. ABBE NUMBER(Vd): 100
3. COATING: BBAR (700 - 1100nm)
4. FOCUS RANGE: +5 to +10 DIOPTER
5. TRANSMITTED WAVEFRONT ERROR, RMS:
VERTICAL: 0.1λ @ 795nm
HORIZONTAL: 0.17λ @ 795nm
6. DAMAGE THRESHOLD, CW: 10 kW/cm² @ 1064nm
7. ROHS COMPLIANT

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

EO® **Edmund Optics®**

THIRD ANGLE PROJECTION 		TITLE	+5 TO +10 DIOPTERS, NIR COATED, FOCUS TUNABLE LENS	
ALL DIMS IN	mm	DWG NO	88938	SHEET 1 OF 1