NOTES:

- 1. SUBSTRATE:FUSED SILICA
- 2. SURFACE S2 TO BE PARALLEL WITH SURFACE S1 TO WITHIN <3 <3 ARCMIN
- 3. COATING (APPLY ACROSS COATING APERTURE): S1: R(ABS) > 99% @ 1064nm T(ABS) > 95% @ 355nm @ 45° AOI

DAMAGE THRESHOLD (PULSED): 7.5 J/cm² @ 20ns , 20 Hz @ 1064nm 2.5 J/cm² @ 20ns , 20 Hz @ 355nm


S2: R(ABS) < 0.25% @ 355nm @ 45° AOI


DAMAGE THRESHOLD (PULSED): 7.5 J/cm² @ 20ns , 20 Hz @ 355nm




5. ROHS COMPLIANT









SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

Edmund Ontics®

	\$1	\$2		
SHAPE	PLANO	PLANO		
SURFACE QUALITY	10-5	10-5		
CLEAR APERTURE	Ø10.80	Ø10.80		
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED		

			Lamara Optics		
THIRD ANGLE PROJECTION		TITLE	Ø12.7mm HS 532, 1064R/355T HARMONIC BEAMSPLITTER		
)	ALL DIMS IN	mm	DWG NO	37714	SHEET 1 OF 1