






- 1. SUBSTRATE: SF10
- 2. Coating: UNCOATED
- 3. Group Velocity Dispersion (fs2/mm): 155 @ 800nm
- 4. ROHS COMPLIANT



**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

REV. A	
TYPE	DISPERSION PRISM
ANGLE TOL. (arcmin)	±3
CLEAR APERTURE	>80%
GROUP VELOCITY DISPERSION (fs <sup>2</sup> /mm)	155
SURFACE QUALITY	40-20
SURFACE FLATNESS	λ/10
BEVEL	PROTECTIVE AS NEEDED

THIRD ANGLE PROJECTION 			
TITLE		25.4 x 25.4mm, SF10, ULTRAFast PRISM	
ALL DIMS IN	mm	DWG NO	89844
		SHEET 1 OF 1	