

1. SUBSTRATE SAPPHIRE (AI2O3)

## *FOR INFORMATION ONLY:* DO NOT MANUFACTURE PARTS TO THIS DRAWING

2. SURFACE S2 TO BE PARALLEL WITH SURFACE S1 TO WITHIN 3.5 ARCMIN

3. COATING (APPLY ACROSS CLEAR APERTURE)


S1: R(ABS) ≤ 1.5% FROM 750-800nm @ 0° AOI R(ABS) ≤ 1.0% FROM 800-1550nm @ 0° AOI R(AVG) ≤ 0.7% FROM 750-1550nm @ 0° AOI


S2: R(ABS) ≤ 1.5% FROM 750-800nm @ 0° AOI R(ABS) ≤ 1.0% FROM 800-1550nm @ 0° AOI R(AVG) ≤ 0.7% FROM 750-1550nm @ 0° AOI



4. POWER, IRREGULARITY, AND SURFACE QUALITY SPECIFICATIONS APPLY ACROSS CLEAR APERTURE

5. ROHS COMPLIANT





	\$1	\$2	SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY				
SHAPE	PLANO	PLANO				®	
CLEAR APERTURE	Ø22.5	Ø22.5				Edmund Optic	<b>C</b> ®
SURFACE FLATNESS	2λ	2λ					J3"
SURFACE ROUGHNESS	0.1 MICRONS PER INCH	0.1 MICRONS PER INCH			TITLE	25mm DIAMETER, NIR II COATED SAPPHIRE	
SURFACE QUALITY	80-50	80-50	THIRD ANGLE. PROJECTION	$\bigcirc \bigcirc$		WINDOW	
BIREFRINGENCE (n <sub>o</sub> -n <sub>e</sub> )	0.008	0.008	ALL DIMS IN	mm	DWG NO		
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED				36576	SHEET 1 OF 1