





**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**



BANDPASS FILTER

| REV. 001                   | VALUE                                   |
|----------------------------|---|
| CENTER WAVELENGTH (CWL)    | 1450nm ±2nm                             |
| FULL WIDTH HALF MAX (FWHM) | 10.0 ±2nm                               |
| MINIMUM TRANSMISSION       | ≥85%                                    |
| BLOCKING                   | 400 - 1800nm                            |
| SURFACE QUALITY            | 80-50                                   |
| CONSTRUCTION               | MOUNTED IN BLACK ANODIZED ALUMINUM RING |
| COATING TYPE               | Hard Coated                             |
| DURABILITY                 | MIL-C-48497a, SEC 3.4.1                 |
| ENVIRONMENTAL              | MIL-STD-810F, SEC 507.4                 |

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY



|                        |    |        |                                |              |
|------------------------|----|--------|--------------------------------|--------------|
| THIRD ANGLE PROJECTION |    | TITLE  | Filter BP 1450 x 10nm OD4 50mm |              |
| ALL DIMS IN            | mm | DWG NO | 39326                          | SHEET 1 OF 1 |