## NOTES:


SHAPE

- 1. SUBSTRATE: SAPPHIRE (AL2O3)
- 2. SURFACE S2 TO BE PARALLEL WITH SURFACE S1 TO WITHIN ≤ 3.5 ARCMIN
- 3. COATING (APPLY ACROSS CLEAR APERTURE)

S1 & S2: R(AVG) <1% @ 1650 - 3000nm R(ABS) <2% @ 1650 - 3000nm

4. FINE GRIND SURFACE

5. ROHS COMPLIANT



INFORMATION ON

DO NOT MANUFACTURE

PARTS TO THIS DRAWING

FOR

CLEAR APERTURE	Ø9.00	Ø9.00	-			Edmund Optic	<b>C</b> ®
SURFACE FLATNESS	2λ	2λ					5
SURFACE ROUGHNESS	0.1 MICRONS PER INCH	0.1 MICRONS PER INCH				10mm DIAMETER, BBAR (1650-3000nm	
SURFACE QUALITY	80-50	80-50			TITLE	COATED SAPPHIRE WINDOW	
BIREFRINGENCE (n <sub>o</sub> -n <sub>e</sub> )	0.008	0.008					CUEFT
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED	ALL DIMS IN	mm	DWG NO	15990	SHEET 1 OF 1