


NOTES:

1. SUBSTRATE: D-ZK3

2. COATING (APPLY ACROSS CLEAR APERTURE)

S1 & S2:BBAR (600-1050nm)
Rabs <1.0% @ 600 - 1050nm



FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING

	S1	S2
SHAPE	CONVEX	PLANO
SURFACE QUALITY	60-40	60-40
CLEAR APERTURE (mm)	Ø 5.75	Ø 5.75
NUMERICAL APERTURE	0.44	0.44
TRANSMITTED WAVEFRONT	<0.05 WAVES RMS @ 632.8nm	<0.05 WAVES RMS @ 632.8nm
OPERATING TEMPERTURE (°C)	≤200	≤200
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

EFL @ 515nm:
6.7 ±0.067

THIRD ANGLE
PROJECTION

ALL DIMS IN

mm

 **Edmund Optics®**

TITLE

LightPath 354525 | 6.65mm Dia., 0.44 NA,
BBAR (600-1050nm), Molded Aspheric Lens

DWG NO

19702

SHEET

1 OF 1