

NOTES:

1. SUBSTRATE: N-SF5

2. COATING (APPLY ACROSS CLEAR APERTURE)

S1 & S2: SWIR+ (900-1700nm)

R(AVG) <0.5% @ 900 - 1700nm @ ±30° AOI

R(ABS) <1% @ 900 - 1700nm @ ±30° AOI



3. EDGES: FINE GROUND

4. CENTERING: <3 ARCMIN

5. ASPHERE FIGURE ERROR: 0.25µm RMS

6. ASPHERIC SURFACE DESCRIBED BY (REF. COEFFICIENT TABLE)

$$Z_{ASPH}(Y) = \frac{(1/RADIUS) * Y^2}{1 + \sqrt{1 - (1+k) * (1/RADIUS)^2 * Y^2}} + D * Y^2 + E * Y^4 + F * Y^6 + G * Y^8 + H * Y^{10} + J * Y^{12} + L * Y^{14}$$



SECTION A-A

COEFFICIENT TABLE 6.

COEFFICIENT	S1
SEMI-DIAMETER	1.500000E+01
(1/RADIUS)	0.495491E-01
k	-1.437343E+00
D	0.000000E+00
E	1.308910E-05
F	-2.034933E-09
G	9.382489E-13
H	-2.402496E-15
J	0.000000E+00
L	0.000000E+00

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2	EFL @ 587.6nm	30.00		Edmund Optics® 30mm Dia., 0.50 Numerical Aperture, 900-1700nm Coated, Inked, High Precision Aspheric Lens		
SHAPE	CONVEX	PLANO	BFL @ 587.6nm	22.53				
RADIUS	20.182	INFINITY	THIRD ANGLE PROJECTION	TITLE	DWG NO	17003INK	SHEET 1 OF 1	
SURFACE QUALITY	40-20	40-20						
CLEAR APERTURE	Ø27.00	Ø27.00						
BEVEL MAX	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED	ALL DIMS IN	mm				