

TECHSPEC® 0.037X, 1/1.8" C-Mount TitanTL® Telecentric Lens



TitanTL® Telecentric Lens

Stock **#34-003** ☐ In Stock

1

C\$13,349.00

ADD TO CART

Qty 1+

C\$13,349.00

Volume Pricing

[Request Quote](#)

Get Product Downloads

Horizontal Field of View, 1/2" Sensor:
172.4mm

Weight (kg):
10

Numerical Aperture NA, Object Side:
0.0023

Resolution, Image Space:
70 lp/mm @45% (MTF, open)

Number of Elements (Groups):
6 (4)

Note: TitanTL®
Horizontal Field of View, 1/1.8" Sensor: 193.9mm
Type: Telecentric Lens
Primary Magnification PMAG: 0.037X
Maximum Sensor Format: 1/1.8"
Working Distance (mm): 379
Mount: C-Mount
Aperture (f/#): f/8 - f/16
Coating: λ/4 MgF ₂
Depth of Field (mm): ±284.2mm (20% @ 20 lp/mm, open)
FOV @ Max Sensor Format, H x V (mm): 194.6 x 145.9
Resolution, Image Space MTF @ F8: 70 lp/mm @ 45%
Rear Filter Diameter (mm): 12.7
Typical Distortion @ 520nm (%): <0.09
Typical Telecentricity @ 520nm (°): <0.1
Lens Wavelength Range: VIS

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View