

[See all 36 Products in Family](#)

0.1 - 4.0 OD, 75 x 75mm, Kodak Wratten 2 Neutral Density Filter Kit (13 Filters)



Stock #15-115 [CONTACT US](#)

1 [+](#) [-](#) C\$3,836⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	C\$3,836.00 each
Need More?	Request Quote

Product Downloads

General

Filters Included:
Optical Densities: [0.1](#), [0.2](#), [0.3](#), [0.4](#), [0.5](#), [0.6](#), [0.7](#), [0.8](#),
[0.9](#), [1.0](#), [2.0](#), [3.0](#), [4.0](#)

Type:
Neutral Density Filter

Number of Filters:
13

Physical & Mechanical Properties

Dimensions (mm):
75 x 75 (Nominal)

75.00 Length (mm):

75.00 Width (mm):

Regulatory Compliance

[View](#)

Certificate of Conformance:

Product Details

- Available in Large Sizes
- Easily Cut for Custom Sizing
- Kodak Filter No. 96

Kodak Wratten 2 Neutral Density Filters are used in image forming optical systems to reduce light intensity across the visible spectrum without altering the spectral profile. These ND filters feature tolerances of $\pm 10\%$ of the nominal diffuse density. Although the filters transmit the infrared spectrum, neutrality is controlled only in the visible spectrum. Kodak Wratten 2 Neutral Density Filters are uncoated and have a blocking wavelength range of 400-700nm. All ND filters are 0.1mm in thickness and can be cut for easy custom sizing.

Note: Storage in humid environments can cause the filters to cloud and temperatures should not exceed 50°C for extended periods. Every 0.3 density increment equals one f-stop.

Special Handling

These optics require special handling to avoid damage and ensure long-term performance. Proper handling, cleaning, and storage are essential to maintain optical quality. Explore our [Optics Cleaning Resources](#) for step-by-step guides and best practices. For personalized assistance, [Email us](#) or [Chat](#) with our technical support team.



Component Handling Tools