NOTES:

SUBSTRATE MATERIAL: 1. **FUSED SILICA**

COATING: 2.

S1: SURFACE ETCHED MULTI-LAYER DIELECTRIC GRATING


S2: ANTI-REFLECTION (AR)


DESIGN WAVELENGTH: 1030 ±10nm 3.

ANGLE OF INCIDENCE: 55.5 ±1°

GROOVE DENSITY: 1600 GROOVES/mm GROOVE UNIFORMITY: 0.001 GROOVES/mm

ROHS COMPLIANT





FOR INFORMATION ONLY: DO NOT MANUFACTURE **PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

	\$1	\$2			
SHAPE	PLANO	PLANO			
SURFACE QUALITY	60-40	60-40			
CLEAR APERTURE	30.80 x 11.30	30.80 x 11.30			
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED			

		I	Eamur
HIRD ANGLE _ ROJECTION	$\phi \lhd$	TITLE	II-VI LightSmyth™ 1030 31.8 x 12.3mm Transm
all DIMS IN	mm	DWG NO	16863

Edmund Optics®				
	II-VI LightSmyth™ 1030nm, 1600 Groove 31.8 x 12.3mm Transmission Diffraction G	s/mm, Grating		
NO	16863	SHEET 1 OF 1		