

TECHSPEC[®] 0.125X, 2/3" GoldTL™ Telecentric Lens



#55-348 (0.125X)

Stock **#55-348** 20+ In Stock

-

1

+

C\$4,628⁷⁵

ADD TO CART

Volume Pricing	
Qty 1+	C\$4,628.75 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

General

GoldTL™ Series

Series:

[#56-027](#) Sold Separately

Stock No. of Mounting Clamp:

Telecentric Lens

Type:


Focusable Telecentric		Special Type of Lens:
Physical & Mechanical Properties		
Variable	Iris Option:	
200.00	Length (mm):	
200.00	Length excluding Threads (mm):	
110.00	Maximum Diameter (mm):	
2.66	Weight (kg):	
Optical Properties		
70.4mm	Horizontal Field of View, 2/3" Sensor:	
57.6mm	Horizontal Field of View, 1/1.8" Sensor:	
51.2mm	Horizontal Field of View, 1/2" Sensor:	
11.00	Maximum Image Circle (mm):	
0.01	Numerical Aperture NA, Object Side:	
>45% @ 40 lp/mm	Resolution, Image Space MTF @ f/10:	
10 (8)	Number of Elements (Groups):	
<0.028	Typical Telecentricity @ 588nm (°):	
0.025	Typical Distortion @ 588nm (%):	
0.125X	Primary Magnification PMAG:	
0.12	Telecentric Lens Magnification:	
132 - 182	Working Distance (mm):	
70.4 x 52.8	FOV @ Max Sensor Format, H x V (mm):	
f/6 - f/25	Aperture (f/#):	
λ/4 MgF ₂	Coating:	
±30.4 at f/10 (20% @ 20 lp/mm)	Depth of Field (mm):	
0.125X	Magnification:	
VS	Lens Wavelength Range:	
Sensor		
2/3"	Maximum Sensor Format:	
2.74	Pixel Size (μm):	
Threading & Mounting		
M105 x 1.00 (Female)	Filter Thread:	
C-Mbunt	Mount:	
Regulatory Compliance		
Compliant	RoHS 2015:	
Compliant	REACH 201:	
View	Certificate of Conformance:	

PRODUCT DETAILS


- High Resolution Telecentric Lens for Measurement and Gauging
- Up to 5 MegaPixels, 3.45µm Pixel Size Sensors
- Up to 2/3", C-Mount Telecentric Lens
- Magnification from 0.06X to 1X

TECHSPEC® GoldTL™ Telecentric Lenses were designed specifically for machine vision and metrology applications. The unique focusable design allows for working distance adjustment, while still providing <0.2° telecentricity. These lenses also feature high resolutions, low distortions, and are available for ½" or 2/3" sensors. TECHSPEC® GoldTL™ Telecentric Lenses have a front filter thread for easy integration of [color filters](#), [polarizers](#) or other mounted components. Both the iris and focusing adjustment positions can be fixed by set screws to remain secure in high vibration environments.


TECHNICAL INFORMATION




#55-348, 0.125X, 2/3" GoldTL™ Telecentric Lens, Distortion Plot




#55-348, 0.125X, 2/3" GoldTL™ Telecentric Lens, Relative Illumination Plot




#55-348, 0.125X, 2/3" GoldTL™ Telecentric Lens, Telecentricity Plot




#55-348, 0.125X, 2/3" GoldTL™ Telecentric Lens, Modulated Transfer Function (MTF) Plot, 157mm Working Distance, f6



#55-348, 0.125X, 2/3" GoldTL™ Telecentric Lens, Depth of Field Plot, 157mm Working Distance, f6



#55-348, 0.125X, 2/3" GoldTL™ Telecentric Lens, Modulated Transfer Function (MTF) Plot, 157mm Working Distance, f10



#55-348, 0.125X, 2/3" GoldTL™ Telecentric Lens, Depth of Field Plot, 157mm Working Distance, f10

Stock No.	A	B	C	D	E	F	G
#56-024	88mm	16mm	34mm	94mm	120mm	101.6mm	50mm

#56-025	85mm	17.5mm	32.5mm	91mm	120mm	101.6mm	48.5mm
#56-026	103mm	—	39.5mm	107mm	103mm	90mm	55.5mm
#56-027	134mm	—	55mm	148mm	134mm	122mm	81mm

