

TECHSPEC® 0.066X, 1" C-Mount TitanTL® Telecentric Lens



TitanTL® Telecentric Lens

Stock **#34-013** ☐ In Stock

1

C\$13,993.00

ADD TO CART

Qty 1+

C\$13,993.00

Volume Pricing

[Request Quote](#)

Get Product Downloads

Horizontal Field of View, 1/2" Sensor:
96.9mm

Horizontal Field of View, 2/3" Sensor:
133.2mm

Weight (kg):
9.94

Horizontal Field of View, 1" Sensor:
193.8mm

Numerical Aperture NA, Object Side:
0.0030

Resolution, Image Space: 50 lp/mm @ 40% (MTF, open)
Number of Elements (Groups): 6 (4)
Note: TitanTL®
Horizontal Field of View, 1/1.8" Sensor: 109.0mm
Type: Telecentric Lens
Primary Magnification PMAG: 0.066X
Maximum Sensor Format: 1"
Working Distance (mm): 377
Mount: C-Mount
Aperture (f/#): f/11 - f/22
Coating: λ/4 MgF ₂
Depth of Field (mm): ±130.9mm (20% @ 20 lp/mm, open)
FOV @ Max Sensor Format, H x V (mm): 193.9 x 145.4
Rear Filter Diameter (mm): 25.4
Typical Distortion @ 520nm (%): <0.05
Typical Telecentricity @ 520nm (°): <0.1
Lens Wavelength Range: VIS

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View