

[See all 76 Products in Family](#)

# LightPath 354260 | 6.5mm Dia., 0.16 NA, BBAR (1050-1600nm), Molded Aspheric Lens

See More by [Lightpath®](#)



Precision Molded Aspheric Lenses

Stock **#37-100** **20+ In Stock**

[Other Coating Options](#)

⊖ 1 ⊕ C\$119<sup>00</sup>

**ADD TO CART**

### Volume Pricing

|            |                               |
|------------|-------------------------------|
| Qty 1-10   | C\$119.00 each                |
| Qty 11-49  | C\$107.10 each                |
| Need More? | <a href="#">Request Quote</a> |

### Product Downloads

### General

Thickness: 0.25 (t) (mm)  
Material: BK7

Compatible Window:

354260

Lightpath Lens Code:

Aspheric Lens

Type:

Collimate or Focus Laser Light

Typical Applications:

## Physical & Mechanical Properties

6.50 ±0.015 Diameter (mm):

5 Clear Aperture CA (mm):

1.8 Edge Thickness ET (mm):

2.21 ±0.05 Center Thickness CT (mm):

Protective as needed Bevel:

12.727 Distance from Window to Lens (D) (mm):

## Optical Properties

15.29 @ 780nm Effective Focal Length EFL (mm):

0.16 Numerical Aperture NA:

D-ZK3 Substrate: □

±1 Focal Length Tolerance (%):

780 Aspheric Design Wavelength (nm):

BBAR (1050-1600nm) Coating:

R<sub>abs</sub> <1.0% @ 1050 - 1600nm Coating Specification:

40-20 Surface Quality:

3.12 f#:

50.22 Abbe Number (v<sub>d</sub>):

1.586 Index of Refraction (n<sub>d</sub>):

1050 - 1600 Wavelength Range (nm):

13.98 Working Distance (mm):

Infinite Conjugate Distance:

780.00 Focal Length Specification Wavelength (nm):

< 0.09 Transmitted Wavefront Error (λ, RMS):

## Material Properties

7.6 Coefficient of Thermal Expansion CTE (10<sup>-6</sup>/°C):

## Environmental & Durability Factors

≤200 Operating Temperature (°C):

## Regulatory Compliance

Compliant RoHS 2015:

View Certificate of Conformance:

Compliant Reach 247:

## Product Details

- Eliminate Spherical Aberration
- Multiple Coating Options Available
- Range of Numerical Apertures

LightPath® Geltech™ Molded Aspheric Lenses are used to eliminate spherical aberration and improve focusing and collimating accuracy in a variety of laser applications. Low NA aspheric lenses are designed to maintain beam shape, while high NA lenses gather all available light to maintain beam power over long distances. LightPath® Geltech™ Molded Aspheric Lenses are ideal for applications including sighting systems, bar code scanners, laser



### Technical Information



### Compatible Mounts