

0.19 - 20 μ m, 15J, Pyroelectric Energy Detector



0.19 - 20 μ m, 15J, Pyroelectric Energy Detector

Stock #78-469 **1 In Stock**

- 1 + C\$4,312⁰⁰

ADD TO CART

Volume Pricing

Qty 1-4	C\$4,312.00 each
Qty 5+	C\$3,885.00 each
Need More?	Request Quote

Product Downloads

General

QE50LP-H-MB-INT-D0 **Model Number:**

Heatsink **Cooling Method:**

1 of (#15-267) is included **Note:**

15 **Maximum Incident Energy (J):**

Compatible Meters:

Physical & Mechanical Properties

75 x 75 x 44	Dimensions (mm):
338	Weight (g):
0.34	Weight (kg):
50 x 50	Active Area (mm):

Optical Properties

190 - 20000	Wavelength Range (nm):
0.19 - 20	Wavelength Range (µm):

Sensor

Pyroelectric	Type of Sensor:
--------------	------------------------

Electrical

20,000	Maximum Incident Beam Power (mW):
20	Maximum Incident Beam Power (W):
0.6	Maximum Incident Energy Density (J/cm², 10ns Pulses):
10 µJ	Noise Level:

Regulatory Compliance

View	Certificate of Conformance:
----------------------	------------------------------------

Product Details

- Photodetectors, Thermopiles, and Pyroelectric Detectors Available
- Various Active Area Sizes Across a Wide Range of Sensitivities
- [Meterless](#) and [Wireless](#) Detectors Also Available

Gentec-EO Integra USB Power and Energy Detectors combine a power meter and detector in one convenient package while providing fast response times and accurate measurements for beam analysis. These detectors are designed with a USB connector for easy connection to a PC or other acquisition system and include user-friendly software allowing for control via PC or serial commands. Versatile pyroelectric energy detectors with broadband coatings are optimized for low to high power densities. Gentec-EO Integra USB Power and Energy Detectors can be used with a variety of laser powers ranging from the nanowatts to multi-kilowatts. These detectors are ideal for laser energy measurement, thermal imaging, and remote sensing applications.