

# 0.15 OD 50mm Sq, Absorptive ND Filter

See More by [Hoya](#)



Stock **#46-217** ☐ In Stock

-

1

+

C\$133.00

ADD TO CART

|                               |
|-------------------------------|
| Qty 1-10                      |
| C\$133.00                     |
| Qty 11+                       |
| C\$117.60                     |
| Volume Pricing                |
| <a href="#">Request Quote</a> |

Get Product Downloads



Dimensions (mm):  
50.0 x 50.0

Optical Density OD (Average):  
0.15 ±0.04

|                                                                    |
|--------------------------------------------------------------------|
| <div>Glass/Filter Number:<br/><a href="#">Hoya ND-70</a></div>     |
| <div>Substrate: <input type="checkbox"/><br/>ND Filter Glass</div> |
| <div>Length (mm):<br/>50.00</div>                                  |
| <div>Coating:<br/>Uncoated</div>                                   |
| <div>Index of Refraction <math>n_d</math>:<br/>1.50</div>          |
| <div>Surface Quality:<br/>80-50</div>                              |
| <div>Transformation Temperature (°C):<br/>470</div>                |
| <div>Thickness (mm):<br/>2.50</div>                                |
| <div>Thickness Tolerance (mm):<br/>±0.5</div>                      |
| <div>Transmission (%):<br/>70.0 (average)</div>                    |
| <div>Type:<br/>Neutral Density Filter</div>                        |
| <div>Width (mm):<br/>50.00</div>                                   |
| <div>Blocking Wavelength Range (nm):<br/>400 - 700</div>           |
| <div>Dimensional Tolerance (mm):<br/>±0.2</div>                    |
| <div>Parallelism (mm):<br/>&lt;0.02</div>                          |

## Regulatory Compliance

|                                                                 |
|-----------------------------------------------------------------|
| <div>RoHS 2015:<br/><a href="#">Compliant</a></div>             |
| <div>REACH 201:<br/><a href="#">Compliant</a></div>             |
| <div>Certificate of Conformance:<br/><a href="#">View</a></div> |