

[See all 19 Products in Family](#)

## 0.22 NA UV/VIS Patchcord 400 Micron Fiber w/ SMA Connector



Stock #23-695 **5 In Stock**

- 1 + C\$359<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-4	C\$359.80 each
Qty 5-10	C\$324.80 each
Qty 11-24	C\$288.40 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### General

Patchcord **Type:**  
Multimode **Fiber Cable Type:**

### Physical & Mechanical Properties

1.5 **Length (m):**

400 Core Diameter (µm):

PVC MONOCOIL (0.190" OD) Jacket Material:

## Optical Properties

Nylon Coating Type:

0.22 Numerical Aperture NA:

UV-VIS Wavelength:

## Hardware & Interface Connectivity

SMA905 Connector:

## Environmental & Durability Factors

-40 to +100 Operating Temperature (°C):

## Regulatory Compliance

Compliant RoHS 2015:

View Certificate of Conformance:

Compliant Reach 250:

## Product Details

- UV/VIS and VIS/NIR Versions Available
- FC Connector Compatible with [Spatial Filters](#)
- FC Connector Compatible with [Fiber Alignment Mounts](#)
- FC and SMA Connector Options

High Quality Fiber Patchcords are designed for UV-VIS (190 - 1250nm) or VIS-NIR (300 - 2400nm) ranges. These Patchcords are 1.5 meters in length with Nylon or Tefzel coatings. With core diameters ranging from 50 – 1000µm, these patchcords provide quality solutions for a variety of core sizes. High Quality Fiber Patchcords are available with SMA905 or FC/PC connectors featuring a 0.22 numerical aperture. These Patchcords are ideal for applications requiring optimum transmission in the UV-VIS or VIS-IR wavelengths.

## Technical Information

