

[See all 77 Products in Family](#)

LightPath 354260 | 6.5mm Dia., 0.16 NA, BBAR (1050-1600nm), Molded Aspheric Lens

See More by [Lightpath®](#)



Precision Molded Aspheric Lenses

Stock **#37-100** **20+ In Stock**

[Other Coating Options](#)

-

1

+

C\$119⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-10	C\$119.00 each
Qty 11-49	C\$107.10 each
Need More?	Request Quote

Product Downloads


General	
Thickness: 0.25 (t) (mm) Material: BK7	Compatible Window:
354260	Lightpath Lens Code:
Aspheric Lens	Type:

Typical Applications: Collimate or Focus Laser Light	
Physical & Mechanical Properties	
Diameter (mm):	6.50 ±0.015
Clear Aperture CA (mm):	5
Edge Thickness ET (mm):	1.8
Center Thickness CT (mm):	2.21 ±0.05
Bevel:	Protective as needed
Distance from Window to Lens (D) (mm):	12.727
Optical Properties	
Effective Focal Length EFL (mm):	15.29 @ 780nm
Numerical Aperture NA:	0.16
Substrate: □	D-ZK3
Focal Length Tolerance (%):	±1
Aspheric Design Wavelength (nm):	780
Coating:	BBAR (1050-1600nm)
Coating Specification:	R _{abs} <1.0% @ 1050 - 1600nm
Surface Quality:	40-20
f/#:	3.12
Wavelength Range (nm):	1050 - 1600
Working Distance (mm):	13.98
Conjugate Distance:	Infinite
Transmitted Wavefront Error (λ, RMS):	< 0.09
Environmental & Durability Factors	
Operating Temperature (°C):	≤200
Regulatory Compliance	
RoHS 2015:	Compliant
Certificate of Conformance:	View
Reach 247:	Compliant


Product Details

- Eliminate Spherical Aberration
- Multiple Coating Options Available
- Range of Numerical Apertures

LightPath® Geltech™ Molded Aspheric Lenses are used to eliminate spherical aberration and improve focusing and collimating accuracy in a variety of laser applications. Low NA aspheric lenses are designed to maintain beam shape, while high NA lenses gather all available light to maintain beam power over long distances. LightPath® Geltech™ Molded Aspheric Lenses are ideal for applications including sighting systems, bar code scanners, laser diode-to-fiber coupling, optical data storage, or biomedical lasers.



Technical Information



Compatible Mounts

;