

# LightPath 354560 | 6.33mm Dia., 0.18 NA, BBAR (1050-1600nm), Molded Aspheric Lens

See More by [Lightpath®](#)



Precision Molded Aspheric Lenses

Stock **#48-160** CLEARANCE ☐ **In Stock**

[Other Coating Options](#)

1

C\$55.93

ADD TO CART

Qty 1+

C\$55.93

Volume Pricing

[Request Quote](#)

Get Product Downloads

**Diameter (mm):**  
6.33 ±0.015

**Effective Focal Length EFL (mm):**  
13.86 @ 650nm

**Numerical Aperture NA:**  
0.18

**Substrate:** ☐  
[D-ZK3](#)

|                                                                         |
|-------------------------------------------------------------------------|
| <b>Focal Length Tolerance (%):</b><br>±1                                |
| <b>Aspheric Design Wavelength (nm):</b><br>650                          |
| <b>Coating:</b><br>BBAR (1050-1600nm)                                   |
| <b>Coating Specification:</b><br>R <sub>abs</sub> <1.0% @ 1050 - 1600nm |
| <b>Surface Quality:</b><br>40-20                                        |
| <b>Clear Aperture CA (mm):</b><br>5.10                                  |
| <b>Edge Thickness ET (mm):</b><br>2.280                                 |
| <b>Center Thickness CT (mm):</b><br>2.77 ±0.05                          |
| <b>f/#:</b><br>2.78                                                     |
| <b>Bevel:</b><br>Protective bevel as needed                             |
| <b>Lightpath Lens Code:</b><br>354560                                   |
| <b>Operating Temperature (°C):</b><br>≤200                              |
| <b>Type:</b><br>Aspheric Lens                                           |
| <b>Wavelength Range (nm):</b><br>1050 - 1600                            |
| <b>Typical Applications:</b><br>Collimate or Focus Laser Light          |
| <b>Working Distance (mm):</b><br>12.11                                  |
| <b>Conjugate Distance:</b><br>Infinite                                  |

## Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
| <b>Reach 233:</b><br><a href="#">Compliant</a>             |