

LightPath 354060 | 6.33mm Dia., 0.27 NA, BBAR (350-700nm), Molded Aspheric Lens

See More by [Lightpath®](#)



Stock **#83-697** ☐ In Stock

[Other Coating Options](#)



1



C\$91.00

ADD TO CART

Qty 1-10

C\$91.00

Qty 11+

C\$80.50

Volume Pricing

[Request Quote](#)

Get Product Downloads

Diameter (mm):
6.33 ±0.015

Effective Focal Length EFL (mm):
9.60 @ 633nm

Numerical Aperture NA:
0.27

Substrate: D-ZK3
Focal Length Tolerance (%): ±1
Aspheric Design Wavelength (nm): 633
Coating: BBAR (350-700nm)
Coating Specification: R _{avg} ≤0.5% @ 350 - 700nm
Surface Quality: 60-40
Clear Aperture CA (mm): 5.20
Edge Thickness ET (mm): 1.57
Center Thickness CT (mm): 2.49 ±0.05
f/#: 1.85
Bevel: Protective bevel as needed
Lightpath Lens Code: 354060
Type: Aspheric Lens
Wavelength Range (nm): 350 - 700
Working Distance (mm): 8.100
Conjugate Distance: Infinite

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant