

# LightPath 354060 | 6.33mm Dia., 0.27 NA, BBAR (600-1050nm), Molded Aspheric Lens

See More by [Lightpath®](#)



Stock **#83-698** ☐ In Stock

[Other Coating Options](#)

-

1

+

C\$91.00

ADD TO CART

|                               |
|-------------------------------|
| Qty 1-10                      |
| C\$91.00                      |
| Qty 11+                       |
| C\$80.50                      |
| Volume Pricing                |
| <a href="#">Request Quote</a> |

## Get Product Downloads

Diameter (mm):  
6.33 ±0.015

Effective Focal Length EFL (mm):  
9.60 @ 633nm

Numerical Aperture NA:  
0.27

|                                                                        |
|------------------------------------------------------------------------|
| <b>Substrate:</b> <a href="#">D-ZK3</a>                                |
| <b>Focal Length Tolerance (%):</b><br>±1                               |
| <b>Aspheric Design Wavelength (nm):</b><br>633                         |
| <b>Coating:</b><br>BBAR (600-1050nm)                                   |
| <b>Coating Specification:</b><br>R <sub>abs</sub> <1.0% @ 600 - 1050nm |
| <b>Surface Quality:</b><br>60-40                                       |
| <b>Clear Aperture CA (mm):</b><br>5.20                                 |
| <b>Edge Thickness ET (mm):</b><br>1.57                                 |
| <b>Center Thickness CT (mm):</b><br>2.49 ±0.05                         |
| <b>f/#:</b><br>1.85                                                    |
| <b>Bevel:</b><br>Protective bevel as needed                            |
| <b>Lightpath Lens Code:</b><br>354060                                  |
| <b>Type:</b><br>Aspheric Lens                                          |
| <b>Wavelength Range (nm):</b><br>600 - 1050                            |
| <b>Working Distance (mm):</b><br>8.100                                 |
| <b>Conjugate Distance:</b><br>Infinite                                 |

### Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
| <b>Reach 233:</b><br><a href="#">Compliant</a>             |